


## Peak Flow Meter

Model: PF120A / PF120C



### Color-coded indicators

Adjust to delineate a patient's green (good), yellow (warning) and red (dangerous) zones.



### Easy-to-read numbers

### PF120A

- Compact, lightweight and portable
- Built-in flexible three-zone management system
- Easy-to-read numbers
- Measurement Range 60-800 L/min
- Accuracy and repeatability assurance
- Suitable for use with disposable mouthpiece
- Design for adult
- Washable
- EN ISO 23747 : 2009 compliance
- CE approval

### PF120C

- Compact, lightweight and portable
- Built-in flexible three-zone management system
- Easy-to-read numbers
- Measurement Range 50-400 L/min
- Accuracy and repeatability assurance
- Suitable for use with disposable mouthpiece
- Design for child
- Washable
- EN ISO 23747 : 2009 compliance
- CE approval

### Disposable mouthpiece



Model	Qty per carton	Carton volume
PF120A/PF120C	200 pcs	0.124 cbm/ctn
QTY per 20'	QTY per 40'	QTY per 40'HQ
45000 pcs	90000 pcs	104600 pcs

● Storage Condition  
10°C to 35°C, 30-75% RH

[www.rossmax.com](http://www.rossmax.com)

OBM\_Epaper\_PFM\_ver1448